



Electrofusion Elbow 90°

PN 10			
Dn	L	A	D
315*90°	460	135	4.7/4.0
355*90°	540	140	4.7/4.0
400*90°	570	145	4.7/4.0
500*90°	685	150	4.7/4.0
630*90°	850	185	4.7/4.0
710*90°	960	211	4.7/4.0
800*90°	1070	225	4.7/4.0

PN 16			
Dn	L	A	D
25*90°	82	45	4.7/4.0
32*90°	87	44	4.7/4.0
40*90°	90	45	4.7/4.0
50*90°	115	54	4.7/4.0
69*90°	130	54	4.7/4.0
75*90°	145	60	4.7/4.0
90*90°	164	68	4.7/4.0
110*90°	198	74	4.7/4.0
125*90°	220	80	4.7/4.0
140*90°	239	75	4.7/4.0
160*90°	254	95	4.7/4.0
200*90°	320	105	4.7/4.0
225*90°	360	110	4.7/4.0
250*90°	400	125	4.7/4.0
280*90°	430	130	4.7/4.0
315*90°	480	135	4.7/4.0
315*90° (short)	445	109	4.7/4.0
355*90°	520	140	4.7/4.0
400*90°	580	145	4.7/4.0
450*90°	640	154	4.7/4.0
500*90°	690	151	4.7/4.0
560*90°	755	165	4.7/4.0
630*90°	860	185	4.7/4.0

PN 20			
Dn	L	A	D
50*90°	115	55.6	4.7/4.0
63*90°	131	55	4.7/4.0
75*90°	147	60	4.7/4.0
90*90°	213	70	4.7/4.0
110*90°	200	75	4.7/4.0
160*90°	270	95	4.7/4.0
200*90°	332	100	4.7/4.0
250*90°	410	126	4.7/4.0
315*90°	485	138	4.7/4.0

PN 25			
Dn	L	A	D
110*90°	215	86	4.7/4.0
160*90°	272	99	4.7/4.0
200*90°	303	88	4.7/4.0